

Phase-Stable Flexible Cable TNC-Male to TNC-Male
CBN-3FT-TMTM+

Typical Performance Data

FREQ.	INSERTION LOSS	TNC-MALE RETURN LOSS IN	TNC-MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.03	41.36	41.12
1	0.37	48.58	47.91
2	0.54	43.22	44.48
3	0.66	41.91	43.53
4	0.76	38.93	43.02
5	0.86	39.20	37.12
6	0.94	37.33	36.13
7	1.01	38.40	37.00
8	1.07	36.94	39.25
9	1.13	30.75	32.80
10	1.21	28.42	29.31
11	1.29	30.71	31.63
12	1.35	32.20	33.23
13	1.40	34.83	34.76
14	1.45	29.26	28.13
15	1.50	27.19	27.74
16	1.55	29.69	30.24
17	1.61	32.35	32.47
18	1.66	31.53	31.51