

Phase-Stable Flexible Cable TNC-Male to TNC-Male
CBN-6FT-TMTM+

Typical Performance Data

FREQ.	INSERTION LOSS	TNC-MALE RETURN LOSS IN	TNC-MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.07	35.37	35.25
1	0.71	44.65	41.55
2	1.02	43.28	39.43
3	1.27	39.64	37.67
4	1.48	41.54	37.02
5	1.66	37.32	38.12
6	1.83	36.35	40.07
7	1.98	36.80	38.61
8	2.10	35.72	33.35
9	2.23	31.24	28.65
10	2.37	32.96	27.70
11	2.51	33.37	31.76
12	2.63	34.83	34.72
13	2.74	34.65	35.65
14	2.84	30.67	29.26
15	2.94	29.05	29.46
16	3.05	30.19	30.03
17	3.15	32.52	30.05
18	3.26	33.82	32.13