

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	0.03	64.71	1000	0.24
100	0.03	48.36	1100	0.25
300	0.06	36.22	1200	0.27
800	0.11	29.30	1300	0.31
1000	0.13	28.60	1400	0.39
1300	0.17	27.44	1500	0.77
1500	0.28	21.79	1550	1.33
1550	0.44	19.37	1575	3.33
1575	0.71	19.61	1600	13.11
1600	2.29	24.65	1616	13.66
1610	8.43	9.80	1625	0.16
1616	22.00	4.21	1640	5.59
1620	34.37	2.90	1700	2.42
1625	34.43	2.09	1800	0.60
1630	26.33	1.67	1900	0.39
1700	1.47	6.96	2000	0.34
1900	0.40	14.34	2050	0.33
2200	0.38	16.38	2100	0.33
2500	0.37	26.28	2150	0.32
3000	2.83	4.84	2200	0.33
3300	16.41	1.13	2350	0.35
3500	31.06	0.89	2400	0.37
3800	14.08	1.07	2450	0.38
4000	4.83	4.19	2500	0.40