

Adapter, DIN-Male to N-Female**DINM-NF+***Typical Performance Data*

FREQ.	INSERTION LOSS	N-FEMALE VSWR	N-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.00	1.00	1.00
0.04	0.00	1.00	1.00
0.07	0.00	1.00	1.00
0.10	0.00	1.00	1.00
0.15	0.00	1.00	1.00
0.20	0.00	1.00	1.00
0.25	0.00	1.00	1.00
0.30	0.00	1.00	1.00
0.35	0.00	1.01	1.01
0.40	0.00	1.01	1.00
0.45	0.00	1.01	1.00
0.50	0.00	1.01	1.01
0.55	0.00	1.01	1.01
0.60	0.00	1.01	1.01
0.70	0.00	1.01	1.01
0.80	0.01	1.01	1.01
0.90	0.01	1.02	1.01
1.00	0.00	1.02	1.01
1.10	0.01	1.02	1.01
1.20	0.01	1.02	1.01
1.30	0.01	1.02	1.01
1.40	0.01	1.02	1.01
1.50	0.01	1.02	1.01
1.60	0.01	1.03	1.01
1.70	0.01	1.03	1.01
1.80	0.01	1.03	1.01
1.90	0.01	1.03	1.01
2.00	0.01	1.03	1.01
2.10	0.01	1.03	1.01
2.20	0.01	1.03	1.01
2.30	0.01	1.03	1.01
2.40	0.01	1.03	1.01
2.50	0.01	1.03	1.01
2.60	0.01	1.03	1.01
2.70	0.01	1.03	1.01
2.80	0.02	1.03	1.01
2.90	0.02	1.03	1.01
3.00	0.02	1.03	1.02
3.50	0.02	1.03	1.02
4.00	0.02	1.03	1.03
4.50	0.03	1.03	1.04
5.00	0.03	1.02	1.04
6.00	0.04	1.02	1.05