

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.22	55.8	50.2
1000	0.68	38.0	47.3
2000	0.97	39.3	40.2
3000	1.16	32.6	33.3
4000	1.33	37.3	42.1
5000	1.48	41.6	36.4
6000	1.63	32.6	34.4
7000	1.76	28.6	29.2
8000	1.88	28.9	29.2
9000	1.99	27.9	31.0
10000	2.10	36.1	49.8
11000	2.22	27.6	30.4
12000	2.32	26.5	28.1
13000	2.43	25.9	27.8
14000	2.52	27.5	36.5
15000	2.62	26.8	32.2
16000	2.71	26.3	26.1
17000	2.80	26.2	26.5
18000	2.89	30.3	37.6
19000	2.99	25.9	29.6
20000	3.06	29.4	51.9
21000	3.15	25.7	31.7
22000	3.21	28.4	32.5
23000	3.30	28.2	28.2
24000	3.42	25.7	27.8
25000	3.51	26.6	31.4
26000	3.60	26.2	34.6
27000	3.67	27.7	34.6
28000	3.76	25.1	28.5
29000	3.84	24.2	27.8
30000	3.94	23.4	26.9
31000	4.01	22.6	26.6
32000	4.06	24.8	30.7
33000	4.15	23.7	30.2
34000	4.25	21.7	23.4
35000	4.33	21.2	23.6
36000	4.40	22.1	23.2
37000	4.47	22.5	23.4
38000	4.53	24.5	31.6
39000	4.60	22.0	28.6
40000	4.71	21.8	23.3