

Typical Performance Data

FREQUENCY (MHz)	PHASE SHIFT		RETURN LOSS					
	(Deg.)		(dBr)					
	0°C	+50°C	Vc=1V @ 0°C	Vc=10V @ 0°C	Vc=25V @ 0°C	Vc=1V @ +50°C	Vc=10V @ +50°C	Vc=25V @ +50°C
600.0	310.91	302.56	-11.32	-10.01	-9.88	-11.15	-9.91	-9.88
700.0	368.80	357.25	-11.63	-10.42	-9.79	-11.33	-10.27	-9.77
740.0	402.57	390.39	-11.81	-10.68	-9.83	-11.50	-10.51	-9.80
820.0	450.97	440.76	-11.61	-11.23	-9.98	-11.17	-11.02	-9.93
900.0	472.51	464.41	-11.28	-11.46	-10.27	-11.14	-11.26	-10.19
980.0	477.28	470.45	-11.09	-11.22	-10.74	-10.96	-11.10	-10.59
1060.0	466.16	460.26	-11.22	-11.19	-11.33	-11.05	-11.05	-11.10
1140.0	430.97	424.98	-11.87	-11.38	-11.78	-11.54	-11.17	-11.60
1220.0	396.57	386.46	-12.73	-11.50	-11.49	-12.25	-11.28	-11.37
1260.0	390.00	379.35	-12.77	-11.46	-11.45	-12.35	-11.26	-11.29
1340.0	381.80	373.28	-12.13	-11.21	-11.51	-11.90	-11.06	-11.29
1420.0	367.17	361.69	-11.45	-10.99	-11.46	-11.29	-10.91	-11.23
1500.0	345.54	342.13	-10.95	-10.96	-11.25	-10.84	-10.91	-11.08