

**Test Cable, SMA-Male/SMA-Male****FLC-1.5FT-SMSM+***Typical Performance Data*

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.09	1.01	1.04
0.5	0.17	1.03	1.03
1.0	0.23	1.04	1.06
1.5	0.28	1.06	1.07
2.0	0.32	1.07	1.06
2.5	0.35	1.07	1.05
3.0	0.39	1.07	1.07
3.5	0.41	1.06	1.06
4.0	0.44	1.04	1.04
4.5	0.45	1.02	1.02
5.0	0.48	1.02	1.03
5.5	0.50	1.04	1.04
6.0	0.52	1.06	1.05
6.5	0.54	1.09	1.07
7.0	0.58	1.12	1.09
7.5	0.61	1.15	1.12
8.0	0.63	1.17	1.14
8.5	0.61	1.18	1.15
9.0	0.63	1.20	1.16
9.5	0.63	1.21	1.18
10.0	0.58	1.21	1.19
10.5	0.63	1.19	1.17
11.0	0.68	1.17	1.16
11.5	0.66	1.15	1.14
12.0	0.66	1.13	1.14
12.5	0.71	1.11	1.12
13.0	0.72	1.11	1.11
13.5	0.72	1.10	1.11
14.0	0.76	1.09	1.10
14.5	0.86	1.09	1.10
15.0	0.82	1.11	1.10
15.5	0.82	1.12	1.11
16.0	0.90	1.13	1.12
16.5	0.90	1.15	1.14
17.0	0.84	1.14	1.14
17.5	0.90	1.18	1.15
18.0	1.01	1.21	1.19
18.5	0.98	1.23	1.21
19.0	1.01	1.25	1.26
19.5	1.01	1.24	1.26
20.0	1.02	1.20	1.25
20.5	1.03	1.19	1.29
21.0	0.95	1.22	1.28
21.5	1.01	1.19	1.27
22.0	1.08	1.19	1.27
22.5	1.09	1.19	1.28
23.0	1.07	1.19	1.27
23.5	1.05	1.19	1.23
24.0	1.20	1.13	1.21
24.5	1.15	1.10	1.20
25.0	1.10	1.08	1.20
25.5	1.14	1.11	1.20
26.0	1.17	1.17	1.30

