

Fixed Attenuator

FW-10+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	10.02	1.01
50.0	10.03	1.01
100.0	10.05	1.01
500.0	10.10	1.01
1000.0	10.14	1.00
1200.0	10.15	1.01
1400.0	10.16	1.01
1600.0	10.18	1.01
1800.0	10.20	1.01
2000.0	10.21	1.02
2200.0	10.23	1.02
2400.0	10.24	1.02
2600.0	10.26	1.03
2800.0	10.28	1.03
3000.0	10.29	1.04
3200.0	10.31	1.04
3400.0	10.33	1.04
3600.0	10.35	1.05
3800.0	10.37	1.05
4000.0	10.38	1.05
4200.0	10.40	1.05
4400.0	10.42	1.06
4600.0	10.44	1.06
4800.0	10.45	1.06
5000.0	10.47	1.06
5200.0	10.49	1.07
5500.0	10.52	1.07
6000.0	10.57	1.08
6500.0	10.61	1.10
7000.0	10.67	1.12
7500.0	10.72	1.14
8000.0	10.78	1.16
8500.0	10.89	1.19
9000.0	10.83	1.22
9500.0	10.85	1.26
10000.0	10.88	1.28
10500.0	10.88	1.28
11000.0	10.88	1.27
11500.0	10.88	1.26
12000.0	10.89	1.25
12500.0	10.89	1.26
13000.0	10.85	1.24
13500.0	10.83	1.21
14000.0	10.85	1.20
14500.0	10.79	1.18
15000.0	10.81	1.15