

Fixed Attenuator

FW-5+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10.0	5.00	1.02
50.0	5.00	1.02
100.0	5.02	1.01
500.0	5.07	1.01
1000.0	5.10	1.01
1200.0	5.12	1.00
1400.0	5.13	1.00
1600.0	5.14	1.00
1800.0	5.15	1.00
2000.0	5.17	1.00
2200.0	5.17	1.00
2400.0	5.19	1.01
2600.0	5.20	1.01
2800.0	5.22	1.02
3000.0	5.22	1.03
3200.0	5.23	1.03
3400.0	5.25	1.04
3600.0	5.26	1.05
3800.0	5.27	1.06
4000.0	5.28	1.07
4200.0	5.29	1.08
4400.0	5.30	1.08
4600.0	5.31	1.09
4800.0	5.32	1.09
5000.0	5.34	1.10
5200.0	5.35	1.10
5500.0	5.36	1.10
6000.0	5.39	1.10
6500.0	5.42	1.10
7000.0	5.45	1.12
7500.0	5.48	1.15
8000.0	5.51	1.17
8500.0	5.55	1.19
9000.0	5.58	1.20
9500.0	5.66	1.22
10000.0	5.64	1.23
10500.0	5.63	1.23
11000.0	5.63	1.22
11500.0	5.64	1.23
12000.0	5.65	1.25
12500.0	5.68	1.26
13000.0	5.66	1.26
13500.0	5.67	1.25
14000.0	5.67	1.22
14500.0	5.63	1.17
15000.0	5.65	1.11