

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	91.15	0.07
500	77.18	0.16
1000	71.61	0.24
2000	65.59	0.17
3000	61.75	0.04
4000	59.13	0.09
5000	57.25	0.18
6000	55.80	0.16
7000	54.49	0.05
8000	53.24	0.06
9000	51.96	0.13
10000	50.57	0.15
11000	48.97	0.13
12000	47.13	0.11
13000	45.12	0.11
14000	43.05	0.14
15000	41.06	0.16
16000	39.03	0.15
17000	36.85	0.10
18000	34.61	0.10
19000	32.46	0.19
20000	30.17	0.25
21000	27.50	0.28
22000	24.69	0.27
23000	22.01	0.20
24000	18.22	0.26
25000	13.82	0.47
26000	8.79	1.15
27000	3.89	3.56
28000	1.08	11.94
29000	0.64	24.55
29500	0.67	18.37
30000	0.68	17.25
30500	0.67	18.14
31000	0.66	20.40
31500	0.65	23.98
32000	0.64	27.00
32500	0.63	29.80
33000	0.60	30.36
33500	0.56	29.42
34000	0.51	27.22
34500	0.47	26.18
35000	0.44	25.75
35500	0.43	26.43
36000	0.49	27.16
36500	0.58	27.78
37000	0.68	29.37
37500	0.76	36.40
38000	0.85	27.93
38500	0.97	21.13
39000	1.11	20.03