

High Pass Filter

HFCV-ED13423/4

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.3	63.96	0.04
1.0	53.29	0.00
10.0	33.38	0.00
40.0	23.59	0.06
70.0	28.65	0.20
100.0	20.05	0.74
101.0	19.73	0.78
102.0	19.46	0.82
103.0	19.23	0.87
104.0	19.06	0.91
105.0	18.95	0.96
106.0	18.90	1.02
107.0	18.92	1.07
108.0	19.02	1.14
109.0	19.21	1.20
110.0	19.50	1.28
115.0	22.35	1.80
120.0	15.57	2.98
125.0	7.42	6.11
130.0	3.50	13.18
135.0	2.03	29.70
140.0	1.46	24.91
141.0	1.39	23.61
145.0	1.17	21.29
146.0	1.13	21.09
147.0	1.09	20.98
148.0	1.06	20.94
149.0	1.02	20.97
150.0	0.99	21.06
151.0	0.96	21.19
152.0	0.94	21.36
153.0	0.91	21.57
154.0	0.89	21.82
155.0	0.86	22.08
156.0	0.84	22.37
157.0	0.82	22.69
158.0	0.80	23.04
159.0	0.79	23.40
160.0	0.77	23.78
180.0	0.56	26.62
200.0	0.48	21.52
400.0	0.37	18.85
600.0	0.39	20.64
800.0	0.49	18.09
1000.0	0.80	12.73
1110.0	1.18	9.66
1120.0	1.23	9.39
1130.0	1.28	9.12
1140.0	1.33	8.86
1150.0	1.38	8.61