

Metal Shield Band Pass Filter

JCBP-EDU0995

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	82.85	0.00	30.0	53.90
18.0	52.18	0.12	31.5	43.86
20.0	54.80	0.18	33.0	37.32
22.0	34.82	0.31	36.0	29.13
23.0	25.17	0.42	39.0	24.20
24.0	17.71	0.70	41.0	22.08
25.0	11.19	1.56	44.0	19.82
26.0	5.89	3.61	47.0	18.18
27.0	3.65	7.75	51.0	16.50
28.0	1.41	11.89	53.0	16.01
30.0	0.75	18.97	55.0	15.37
51.0	0.46	25.91	60.0	14.66
88.0	0.92	28.18	63.0	14.44
94.0	1.60	14.05	67.0	14.37
97.0	2.85	7.56	70.0	14.55
100.0	5.32	3.97	75.0	14.94
105.0	11.73	1.70	78.0	15.51
110.0	19.33	1.12	78.5	15.53
115.0	27.66	0.93	80.0	15.89
125.0	50.00	0.79	83.0	16.92
148.0	50.36	0.67	85.0	17.73
150.0	51.72	0.67	87.0	19.03
500.0	71.77	0.47	88.0	19.74
900.0	60.57	0.65	90.0	21.63