

Surface Mount High Pass Filter JCHF-ED13026/1

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
5.0	95.68	0.01	5.0	35.92
10.0	77.23	0.03	10.0	18.78
30.0	60.04	0.42	30.0	12.65
50.0	57.13	1.23	50.0	14.12
70.0	51.40	1.09	77.0	11.68
71.0	54.80	1.10	78.0	41.62
72.0	57.99	1.11	79.0	95.15
73.0	57.33	1.14	88.0	35.53
74.0	51.36	1.19	89.0	21.32
75.0	42.98	1.26	90.0	21.70
76.0	34.98	1.41	91.0	21.93
77.0	27.50	1.70	92.0	22.14
78.0	20.16	2.44	93.0	22.04
79.0	13.21	4.60	94.0	21.86
88.0	6.31	2.84	95.0	21.39
89.0	5.54	3.28	96.0	20.66
90.0	4.80	3.84	97.0	19.89
92.0	3.50	5.34	98.0	18.95
94.0	2.48	7.48	100.0	17.87
96.0	1.76	10.39	110.0	10.43
98.0	1.31	14.18	120.0	7.35
100.0	1.06	18.31	130.0	5.85
120.0	0.85	11.17	140.0	5.01
140.0	0.61	13.03	160.0	3.79
180.0	0.32	23.47	180.0	3.01
200.0	0.27	40.82	200.0	2.49
220.0	0.27	28.40	220.0	2.12
240.0	0.28	22.42	240.0	1.85
260.0	0.30	19.43	260.0	1.66
280.0	0.33	17.52	280.0	1.50
300.0	0.36	16.14	300.0	1.38
320.0	0.40	15.07	320.0	1.28
340.0	0.43	14.18	340.0	1.21
360.0	0.47	13.42	360.0	1.14
380.0	0.52	12.76	380.0	1.08
400.0	0.56	12.18	400.0	1.04
420.0	0.60	11.67	420.0	1.01
440.0	0.65	11.20	440.0	0.97
460.0	0.70	10.76	460.0	0.94
480.0	0.75	10.36	480.0	0.91
500.0	0.80	9.98	500.0	0.90