

High Pass Filter

JCHP-EDU0751

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	79.10	0.00	1100.00	3.43
200.00	50.27	0.02	1125.00	4.07
300.00	48.86	0.04	1150.00	4.03
400.00	48.31	0.07	1160.00	3.89
500.00	49.56	0.11	1200.00	2.96
600.00	53.33	0.14	1300.00	1.71
700.00	73.24	0.21	1330.00	1.55
800.00	56.07	0.28	1350.00	1.46
850.00	57.19	0.35	1400.00	1.28
900.00	58.31	0.42	1500.00	1.05
960.00	47.42	0.55	1650.00	0.80
980.00	42.45	0.61	1700.00	0.81
1025.00	29.57	0.80	1800.00	0.73
1050.00	23.41	0.98	1900.00	0.67
1100.00	10.87	2.14	2000.00	0.65
1150.00	3.24	8.63	2200.00	0.61
1160.00	2.47	11.23	2400.00	0.59
1200.00	1.46	26.73	2500.00	0.52
1330.00	0.84	30.32	2600.00	0.48
1350.00	0.80	28.46	2800.00	0.45
1400.00	0.74	23.72	2900.00	0.46
1500.00	0.69	17.41	2950.00	0.55
1650.00	0.87	13.79	3000.00	0.49
1800.00	0.78	13.76	3050.00	0.52
2000.00	0.61	18.43	3200.00	0.56
2500.00	0.82	15.91	3300.00	0.58
2800.00	0.95	15.07	3500.00	0.63
3000.00	0.77	19.62	3700.00	0.61
3500.00	1.11	10.35	3900.00	0.48
4000.00	3.41	4.08	4000.00	0.35