

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)
100	0.05	40.15
200	0.07	33.06
300	0.08	29.01
400	0.10	26.32
500	0.11	24.14
600	0.13	22.55
700	0.15	21.01
800	0.17	19.86
900	0.19	18.84
1000	0.21	17.92
1200	0.25	16.36
1400	0.30	15.07
1600	0.36	14.01
1800	0.41	13.17
2000	0.46	12.52
2200	0.51	11.95
2400	0.55	11.57
2600	0.57	11.35
2800	0.60	11.26
3000	0.61	11.27
3200	0.60	11.46
3400	0.59	11.83
3600	0.57	12.37
3800	0.55	12.85
4000	0.52	13.67
4500	0.47	16.00
5000	0.46	17.94
5500	0.49	18.27
6000	0.55	17.37
6500	0.61	16.66
7000	0.66	17.01
7500	0.62	24.80
8000	0.83	17.96
8500	1.18	12.35
9000	1.52	13.29
9500	3.53	7.82
10000	13.31	1.40
10500	27.11	0.71
11000	44.89	0.62
11500	35.92	0.93
12000	36.04	0.59
12500	38.31	0.56
13000	41.64	0.47
13500	46.21	0.43
14000	52.15	0.42
14500	57.57	0.41
15000	60.44	0.41
15500	50.15	0.47
16000	44.02	0.40
16500	40.75	0.37
17000	39.96	0.42
17500	39.56	0.41
18000	39.06	0.37
18500	38.39	0.49
19000	37.40	0.69
19500	35.66	0.52
20000	32.39	0.50