

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	0.13	41.06
200	0.14	34.10
300	0.15	30.28
400	0.17	27.55
500	0.18	25.39
600	0.19	23.68
700	0.20	22.33
800	0.22	21.04
900	0.23	20.00
1000	0.25	18.95
1500	0.35	15.24
2000	0.47	12.72
2500	0.60	11.11
3000	0.68	10.42
3500	0.70	10.43
4000	0.64	11.22
4500	0.55	12.84
5000	0.47	15.29
5500	0.42	18.38
6000	0.41	21.07
6500	0.41	23.15
7000	0.43	21.98
7500	0.36	21.57
8000	0.39	23.56
8500	0.44	26.27
9000	0.47	28.77
9500	0.52	25.24
10000	0.58	21.44
10500	0.62	20.66
11000	0.67	21.60
11500	0.73	20.51
12000	0.82	17.59
12400	0.95	14.97
13000	1.32	11.15
13500	2.02	7.93
13700	2.65	6.28
14000	4.51	3.72
14500	10.26	1.32
15000	18.25	0.63
15100	20.11	0.57
15550	29.97	0.41
16000	45.42	0.32
16500	36.25	0.28
17000	35.04	0.23
17500	36.37	0.22
18000	38.64	0.18
18500	41.89	0.18
19000	45.83	0.16
19500	51.48	0.14
20000	52.23	0.14
20500	45.46	0.14
21000	39.94	0.14
21500	34.98	0.17
22000	30.08	0.30
22500	27.90	0.42
23000	38.24	0.48
23500	38.98	0.16
24000	35.18	0.10
24500	32.90	0.05
25000	31.36	0.02
25500	29.65	0.06
26000	28.28	0.12