

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	50.97	1	0.15
10.0	0.07	52.72	10	0.16
50.0	0.09	46.12	100	0.16
100.0	0.10	43.27	200	0.15
250.0	0.13	40.22	250	0.15
500.0	0.16	35.62	300	0.15
1000.0	0.23	26.18	400	0.15
2000.0	0.49	26.32	500	0.15
2250.0	0.71	24.90	600	0.16
2500.0	1.30	45.78	700	0.16
2660.0	3.20	11.31	800	0.16
2750.0	7.75	4.68	900	0.17
2800.0	12.34	2.94	1000	0.17
2870.0	20.25	1.89	1100	0.18
2950.0	28.50	1.42	1200	0.19
3000.0	31.28	1.26	1300	0.19
3200.0	33.17	0.96	1400	0.20
3250.0	34.14	0.92	1500	0.22
3750.0	33.11	0.67	1600	0.23
4000.0	29.53	0.56	1700	0.25
4250.0	28.67	0.47	1800	0.27
5500.0	36.13	0.24	1900	0.29
6000.0	38.94	0.26	2000	0.33
6200.0	37.84	0.29	2250	0.46