

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	51.49	1	0.18
10.0	0.07	50.00	10	0.17
50.0	0.08	43.74	100	0.16
100.0	0.09	42.25	200	0.16
250.0	0.12	40.37	250	0.16
500.0	0.15	38.67	300	0.16
1000.0	0.23	25.88	400	0.16
2150.0	0.65	29.72	500	0.16
2250.0	0.79	33.36	600	0.16
2500.0	1.83	18.96	700	0.17
2660.0	7.18	6.05	800	0.17
2750.0	16.68	2.93	900	0.17
2780.0	20.74	2.47	1000	0.18
2850.0	30.94	1.83	1100	0.19
2950.0	38.92	1.36	1200	0.19
3000.0	37.95	1.21	1300	0.20
3200.0	37.16	0.89	1400	0.21
3250.0	38.68	0.84	1500	0.23
3750.0	32.72	0.56	1600	0.24
4000.0	29.91	0.47	1700	0.26
4250.0	29.23	0.39	1800	0.29
5500.0	36.45	0.25	1900	0.32
6000.0	39.37	0.28	2000	0.36
6200.0	38.42	0.28	2150	0.45