

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	51.20	1	0.18
10.0	0.07	49.62	10	0.17
50.0	0.08	43.07	100	0.15
100.0	0.09	41.55	200	0.15
250.0	0.12	39.45	250	0.15
500.0	0.15	42.26	300	0.15
1000.0	0.21	29.37	400	0.15
2000.0	0.41	24.22	500	0.15
2250.0	0.53	25.71	600	0.15
2300.0	0.57	24.82	700	0.16
2660.0	1.45	12.33	800	0.16
2750.0	2.26	9.04	900	0.16
2800.0	3.05	7.31	1000	0.17
2900.0	6.08	4.42	1100	0.17
3000.0	12.21	2.85	1200	0.18
3090.0	21.67	2.34	1300	0.18
3200.0	34.30	2.09	1400	0.19
3300.0	31.43	1.87	1500	0.20
3750.0	40.94	0.97	1600	0.21
4000.0	44.36	0.70	1700	0.22
4250.0	60.85	0.53	1800	0.24
5500.0	43.26	0.21	1900	0.25
5750.0	40.11	0.24	2000	0.27
6000.0	37.85	0.31	2300	0.37