

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	50.92	1	0.19
10.0	0.07	49.05	10	0.17
50.0	0.09	42.12	100	0.15
100.0	0.10	40.75	200	0.15
250.0	0.13	38.33	250	0.15
500.0	0.16	43.79	300	0.15
1000.0	0.23	30.86	400	0.15
2000.0	0.45	30.44	500	0.15
2150.0	0.55	36.80	600	0.16
2300.0	0.69	25.28	700	0.16
2660.0	2.33	10.55	800	0.16
2750.0	4.35	7.03	900	0.16
2800.0	6.55	5.32	1000	0.17
2900.0	14.71	3.13	1100	0.18
3000.0	29.60	2.22	1200	0.18
3090.0	38.42	1.76	1300	0.19
3200.0	43.88	1.41	1400	0.20
3300.0	45.17	1.20	1500	0.21
3750.0	47.67	0.72	1600	0.22
4000.0	43.10	0.58	1700	0.23
4250.0	37.60	0.46	1800	0.25
5500.0	41.51	0.24	1900	0.27
6000.0	38.83	0.34	2000	0.30
6300.0	35.48	0.29	2150	0.35