

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.07	51.22	1	0.20
10.0	0.07	49.86	10	0.18
50.0	0.09	43.90	100	0.16
100.0	0.09	42.85	200	0.16
250.0	0.12	39.50	250	0.16
500.0	0.15	34.86	300	0.16
1000.0	0.23	24.76	400	0.16
2000.0	0.53	25.49	500	0.16
2100.0	0.62	28.01	600	0.16
2300.0	1.01	20.08	700	0.17
2400.0	1.53	14.71	800	0.17
2500.0	2.94	9.59	900	0.17
2600.0	7.39	5.22	1000	0.18
2720.0	21.84	2.79	1100	0.19
2760.0	29.96	2.42	1200	0.19
3000.0	46.74	1.28	1300	0.21
3200.0	36.37	0.93	1400	0.22
3300.0	38.48	0.83	1500	0.23
3750.0	34.43	0.55	1600	0.24
4000.0	30.99	0.45	1700	0.27
4250.0	30.12	0.37	1800	0.29
5500.0	37.73	0.21	1900	0.32
6000.0	39.33	0.28	2000	0.37
6200.0	37.66	0.25	2100	0.42