

Low Pass Filter

LFCV-ED13423/3

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.3	0.34	28.97
1.0	0.34	28.69
5.0	0.37	27.33
10.0	0.41	24.96
15.0	0.46	22.81
20.0	0.53	21.08
22.0	0.56	20.52
23.0	0.58	20.27
24.0	0.59	20.04
25.0	0.61	19.82
30.0	0.69	18.98
35.0	0.78	18.50
40.0	0.86	18.35
45.0	0.95	18.51
50.0	1.03	18.93
55.0	1.11	19.45
60.0	1.21	19.68
65.0	1.34	18.98
70.0	1.54	16.89
75.0	1.87	13.66
80.0	2.48	10.00
85.0	3.64	6.65
90.0	5.59	4.17
95.0	8.31	2.65
100.0	11.50	1.84
105.0	14.82	1.44
110.0	18.10	1.23
115.0	21.23	1.11
120.0	24.16	1.04
130.0	29.38	0.96
140.0	33.77	0.92
150.0	37.44	0.88
160.0	40.58	0.85
170.0	43.38	0.82
180.0	46.04	0.79
190.0	48.74	0.76
200.0	51.72	0.73
250.0	62.94	0.59
300.0	52.85	0.50
350.0	50.47	0.42
400.0	49.80	0.35
450.0	49.89	0.31
500.0	50.43	0.27
600.0	52.72	0.22
700.0	56.78	0.20
800.0	71.08	0.19
900.0	51.79	0.19
1000.0	38.64	0.23
1100.0	18.49	1.19