

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.03	0.27	25.99	0.03	1316.77
0.38	0.51	21.77	0.05	1264.01
0.45	0.67	25.57	0.07	1236.87
0.50	0.95	21.43	0.09	1243.24
0.52	1.14	23.57	0.12	1252.51
0.55	1.93	16.36	0.14	1265.60
0.57	2.83	10.11	0.16	1279.03
0.57	3.32	8.38	0.18	1303.02
0.59	6.19	3.94	0.20	1333.36
0.62	11.87	1.59	0.22	1362.98
0.64	16.77	0.96	0.24	1395.72
0.69	27.85	0.51	0.26	1432.80
0.73	36.69	0.41	0.28	1471.99
0.78	48.00	0.31	0.30	1514.83
0.80	53.88	0.30	0.32	1558.50
0.90	83.13	0.24	0.34	1605.78
1.00	64.93	0.20	0.36	1665.54
10.00	91.90	0.12	0.38	1734.89
50.00	90.56	0.09	0.40	1828.84
100.00	92.36	0.08	0.41	1881.44
300.00	87.55	0.12	0.42	1939.87
500.00	77.84	0.23	0.43	2004.83
800.00	62.82	0.46	0.44	2083.57
1000.00	63.30	0.99	0.45	2153.78