

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.03	0.21	29.54	0.03	858.48
0.50	0.39	26.28	0.07	1834.31
0.60	0.51	34.52	0.10	882.59
0.70	0.79	19.40	0.12	879.38
0.78	1.47	13.88	0.16	887.32
0.80	2.20	8.64	0.18	893.44
0.82	3.59	5.09	0.20	903.94
0.85	6.37	2.60	0.22	914.01
0.89	12.21	1.11	0.24	920.63
0.95	22.23	0.55	0.28	945.81
1.00	28.98	0.43	0.30	957.88
1.12	48.29	0.31	0.32	973.73
5.00	78.39	0.17	0.34	998.01
10.00	86.98	0.18	0.36	1012.25
20.00	90.18	0.16	0.40	1039.67
50.00	92.57	0.11	0.44	1092.01
75.00	91.20	0.12	0.46	1109.65
100.00	89.85	0.11	0.48	1134.53
300.00	87.06	0.14	0.50	1164.91
500.00	78.79	0.45	0.52	1193.79
800.00	64.68	0.30	0.54	1234.81
1000.00	57.74	0.56	0.56	1280.98
1200.00	59.87	1.65	0.58	1336.32
1400.00	54.53	0.72	0.60	1391.93