

Typical Performance Data

CARRIER FREQ. (MHz)	CONVERSION LOSS (dB)	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET (mV)
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
137.0	5.76	35.71	36.70	33.27	33.31	45.22	57.87	79.42	81.57	-0.08
137.5	5.75	35.67	36.51	33.24	33.30	45.22	58.08	79.42	79.88	-0.16
137.9	5.77	35.45	36.52	33.19	33.29	45.30	58.58	78.70	77.98	-0.06
138.2	5.76	35.18	36.15	33.22	33.28	45.40	58.58	79.20	79.38	-0.07
138.4	5.76	35.33	36.27	33.23	33.27	45.50	58.58	78.60	79.78	-0.13
138.8	5.77	35.21	36.25	33.15	33.26	45.69	58.78	80.69	77.68	-0.19
139.3	5.76	35.06	36.14	33.13	33.19	45.79	59.07	78.39	78.87	-0.08
139.6	5.77	35.13	36.06	33.15	33.25	45.80	59.27	77.00	78.97	-0.11
139.8	5.76	35.09	35.94	33.18	33.20	45.78	59.47	76.28	77.87	-0.07
140.1	5.76	35.13	35.90	33.15	33.19	45.89	59.77	77.39	77.17	-0.07
140.5	5.77	34.97	35.99	33.14	33.19	46.10	60.17	74.80	75.37	-0.18
140.8	5.76	34.94	36.12	33.09	33.22	45.98	60.37	77.28	76.87	-0.17
141.0	5.77	34.92	35.98	33.10	33.21	46.09	60.38	76.59	75.38	-0.17
141.5	5.76	34.90	36.02	33.10	33.13	46.20	60.78	75.40	75.98	-0.19
141.9	5.76	34.85	35.86	33.06	33.11	46.28	61.06	75.58	75.06	-0.17
142.2	5.75	34.85	35.95	33.05	33.16	46.39	61.28	76.29	74.88	-0.21
142.4	5.74	34.80	35.96	33.02	33.17	46.38	61.58	75.48	74.48	-0.11
142.7	5.75	34.72	35.93	33.04	33.11	46.30	61.58	74.60	73.38	-0.12
142.8	5.75	34.72	35.91	33.02	33.16	46.39	62.18	75.89	74.98	-0.10
143.0	5.75	34.65	36.01	33.02	33.11	46.49	61.58	75.59	72.48	-0.11