

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.21	34.78	10.0	1.100
100.0	0.13	30.31	100.0	1.190
200.0	0.18	24.10	200.0	1.200
300.0	0.23	21.74	300.0	1.240
400.0	0.26	23.81	400.0	1.330
500.0	0.29	33.18	500.0	1.440
600.0	0.42	19.11	600.0	1.610
700.0	0.49	26.59	700.0	2.030
760.0	0.98	11.83	900.0	1.510
900.0	12.12	0.74	950.0	1.170
950.0	17.08	0.45	1000.0	0.900
1000.0	21.70	0.36	1050.0	0.830
1050.0	25.91	0.29	1100.0	0.730
1100.0	29.86	0.29	1150.0	0.660
1150.0	33.55	0.27	1200.0	0.600
1200.0	37.05	0.25	1240.0	0.580
1250.0	40.40	0.27	1250.0	0.570
1260.0	41.02	0.26	1260.0	0.560
1500.0	54.46	0.26	1500.0	0.440
2000.0	68.05	0.33	2000.0	0.350
2500.0	66.83	0.35	2500.0	0.240
3000.0	64.08	0.38	3000.0	0.230