

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	83.18	0.10	420.0	2.220
200.0	87.50	0.10	430.0	1.930
330.0	81.91	0.10	440.0	0.040
410.0	69.01	0.10	450.0	1.380
430.0	64.76	0.10	480.0	1.800
440.0	63.14	0.10	500.0	0.670
450.0	61.53	0.10	550.0	0.760
480.0	56.69	0.10	610.0	1.260
500.0	53.07	0.20	620.0	1.480
550.0	45.76	0.20	640.0	1.370
610.0	36.92	0.30	650.0	1.220
640.0	32.87	0.30	660.0	1.180
660.0	30.45	0.30	670.0	1.180
670.0	29.21	0.30	700.0	1.230
700.0	25.28	0.40	720.0	1.370
720.0	22.61	0.50	770.0	1.950
770.0	15.62	0.60	790.0	2.350
820.0	9.80	1.20	820.0	2.040
860.0	4.84	2.90	840.0	1.970
880.0	2.75	4.40	860.0	2.880
885.0	2.41	4.90	880.0	3.590
900.0	1.81	6.70	885.0	3.560
920.0	1.40	9.80	900.0	3.220
1000.0	0.57	22.50	920.0	2.580
1560.0	0.53	18.50	1000.0	1.900
1745.0	0.42	15.80	1560.0	0.830
1925.0	0.62	14.00	1650.0	0.820
2015.0	0.59	13.50	1745.0	0.870
2110.0	0.77	12.90	1835.0	0.750
2200.0	0.71	12.20	1925.0	0.730