

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	74.21	0.10	110.0	3.170
30.0	74.57	0.20	120.0	2.560
50.0	75.03	0.20	130.0	1.730
70.0	75.11	0.20	145.0	1.500
90.0	77.67	0.20	150.0	2.070
100.0	71.90	0.20	155.0	1.110
110.0	64.71	0.20	160.0	3.420
120.0	61.50	0.20	165.0	2.570
130.0	54.50	0.20	170.0	2.970
145.0	47.14	0.10	175.0	2.430
150.0	44.66	0.10	180.0	3.140
160.0	39.74	0.10	190.0	3.210
170.0	34.99	0.10	195.0	3.620
175.0	32.61	0.10	200.0	4.110
180.0	30.36	0.10	205.0	4.380
190.0	25.67	0.10	210.0	4.710
195.0	23.38	0.10	220.0	5.850
205.0	18.79	0.30	230.0	7.340
220.0	11.96	0.70	240.0	8.940
230.0	7.65	1.60	245.0	9.280
240.0	4.02	3.60	265.0	7.190
245.0	2.69	5.40	285.0	4.930
265.0	0.66	22.90	290.0	4.530
285.0	0.52	19.60	780.0	0.870
290.0	0.52	18.70	850.0	0.750
850.0	0.28	27.80	920.0	0.720
990.0	0.33	19.60	990.0	0.720
1060.0	0.38	17.10	1060.0	0.750
1130.0	0.42	15.30	1130.0	0.560
1200.0	0.47	15.00	1200.0	0.680