

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	100.92	0.00	395	5.19
10	95.71	0.00	400	4.80
50	85.60	0.00	420	3.65
150	73.94	0.07	450	2.72
210	50.79	0.10	510	1.99
270	31.77	0.23	570	1.52
290	25.71	0.31	600	1.37
310	19.56	0.43	630	1.21
340	10.59	1.06	650	1.13
360	4.95	2.90	690	1.06
370	2.76	5.14	740	0.90
380	1.43	8.92	760	0.87
395	0.71	17.59	850	0.72
450	0.52	16.10	900	0.75
470	0.42	18.70	960	0.66
650	0.45	13.68	1000	0.64
810	0.34	16.47	1130	0.56
920	0.29	22.87	1260	0.48
1100	0.23	22.95	1300	0.45
1350	0.41	14.61	1350	0.47
1600	0.53	13.05	1430	0.49
1730	0.47	13.51	1600	0.38
1860	0.51	14.94	1800	0.42
2000	0.33	18.15	2000	0.43