

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	98.99	0.00	500	3.28
20	84.50	0.00	520	2.72
50	81.96	0.00	550	2.20
150	86.82	0.05	560	2.08
230	56.18	0.13	590	1.82
250	49.97	0.16	600	1.75
320	31.69	0.28	650	1.47
350	24.80	0.35	680	1.34
410	10.66	0.92	700	1.25
454	2.55	5.20	710	1.22
460	1.88	6.64	800	0.95
500	0.48	20.58	900	0.73
530	0.44	17.78	960	0.77
550	0.43	17.51	1000	0.69
560	0.42	17.95	1100	0.64
570	0.41	18.68	1160	0.59
590	0.36	21.05	1200	0.58
600	0.34	22.74	1260	0.54
700	0.28	21.29	1290	0.54
1000	0.34	19.85	1340	0.52
1400	0.35	19.16	1450	0.50
1600	0.39	15.77	1600	0.44
1800	0.50	15.74	1800	0.37
2000	0.35	18.94	2000	0.40