

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	102.20	0.00	600	3.42
10	99.49	0.00	625	2.65
50	90.32	0.00	650	2.20
100	92.66	0.00	675	1.93
200	83.75	0.06	700	1.71
250	69.01	0.09	750	1.48
310	51.96	0.15	800	1.28
350	42.96	0.20	850	1.14
410	30.86	0.30	900	0.98
480	17.29	0.54	950	0.91
510	11.32	0.92	1000	0.83
560	2.83	4.84	1050	0.76
580	1.17	10.14	1100	0.74
600	0.58	20.52	1150	0.68
650	0.51	16.33	1200	0.66
750	0.38	21.78	1250	0.63
900	0.41	17.02	1300	0.60
1000	0.42	16.19	1350	0.58
1100	0.36	18.05	1400	0.55
1200	0.31	21.83	1450	0.54
1300	0.30	23.06	1500	0.49
1400	0.33	19.19	1550	0.50
1500	0.43	16.05	1575	0.51
1600	0.45	14.14	1600	0.49