

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	104.27	0.00	780	2.57
10	96.51	0.01	800	2.20
50	95.09	0.01	850	1.64
100	86.40	0.01	900	1.40
200	86.55	0.05	950	1.24
250	88.14	0.09	1000	1.12
350	60.13	0.17	1050	1.01
400	50.78	0.21	1100	0.92
480	37.53	0.30	1200	0.77
530	29.98	0.35	1300	0.68
580	22.78	0.44	1350	0.66
620	16.99	0.57	1400	0.63
680	8.15	1.44	1450	0.61
720	3.29	4.18	1500	0.59
750	1.17	9.56	1550	0.56
780	0.56	21.25	1600	0.56
800	0.48	33.76	1650	0.52
1000	0.35	34.61	1700	0.51
1200	0.45	17.71	1750	0.52
1600	0.31	22.20	1800	0.45
1800	0.51	17.21	1900	0.47
2000	0.46	15.37	2000	0.44
2200	0.48	17.00	2200	0.41
2400	0.42	24.83	2400	0.40