

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	101.52	0.00	910	2.25
10	102.65	0.01	950	1.72
50	94.83	0.00	1000	1.45
100	95.12	0.00	1050	1.26
200	83.43	0.03	1100	1.14
350	73.77	0.11	1150	1.04
420	60.35	0.16	1200	0.94
470	51.67	0.20	1250	0.87
580	35.98	0.28	1300	0.80
620	30.85	0.32	1350	0.75
700	20.53	0.43	1400	0.71
800	7.32	1.54	1450	0.67
840	3.22	4.21	1500	0.66
870	1.22	8.95	1550	0.62
900	0.57	17.26	1600	0.60
910	0.52	20.71	1650	0.59
950	0.48	19.18	1700	0.55
1000	0.51	16.87	1750	0.57
1100	0.36	24.05	1800	0.50
1300	0.39	19.01	1850	0.51
1500	0.35	19.13	1900	0.52
1700	0.38	20.37	1950	0.45
1900	0.43	15.29	1980	0.43
2000	0.53	13.72	2000	0.46