

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.00	38.30	10.00	0.90
195.00	0.20	15.70	100.00	1.00
380.00	0.40	14.00	195.00	1.00
565.00	0.20	19.00	285.00	0.80
750.00	0.30	25.30	380.00	0.90
930.00	0.50	20.10	470.00	1.00
1000.00	0.60	18.10	565.00	1.10
1180.00	4.30	5.30	655.00	1.10
1200.00	5.70	3.40	750.00	1.10
1300.00	17.70	0.70	840.00	1.20
1420.00	32.20	0.50	930.00	1.40
1500.00	43.80	0.40	1000.00	1.60
1550.00	53.20	0.30	1150.00	2.80
1600.00	58.30	0.30	1180.00	2.40
1620.00	57.90	0.30	1200.00	2.50
1690.00	58.00	0.30	1300.00	1.20
1720.00	55.60	0.20	1400.00	0.50
2000.00	58.70	0.20	1420.00	0.60
2050.00	61.60	0.10	1440.00	1.10
2070.00	62.20	0.10	1500.00	0.40
2100.00	63.00	0.10	1550.00	0.80
2110.00	62.90	0.10	1600.00	1.30
2120.00	62.00	0.10	1620.00	1.10
2130.00	64.70	0.10	1690.00	1.60
2140.00	66.10	0.10	1700.00	1.00
2150.00	64.30	0.10	1720.00	0.30
2160.00	65.10	0.10	1945.00	1.00
2200.00	66.00	0.10	2000.00	1.70
2300.00	70.50	0.10	2050.00	2.10
2500.00	66.00	0.10	2070.00	1.40