

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.00	0.12	21.70	10.00	5.875
50.00	0.20	18.90	30.00	5.932
70.00	0.19	31.60	50.00	6.124
87.50	0.30	18.10	70.00	6.723
107.50	0.34	19.00	87.50	6.973
127.50	0.43	21.20	107.50	7.940
140.00	0.59	18.50	127.50	9.564
147.50	1.11	11.00	140.00	11.710
155.00	3.27	4.30	145.00	13.582
165.00	9.15	1.20	147.50	14.703
180.00	18.50	0.40	150.00	15.571
195.03	26.35	0.20	155.00	15.775
200.03	28.70	0.20	165.00	10.701
205.00	30.89	0.20	170.00	8.263
210.03	33.01	0.20	180.00	5.337
220.04	36.90	0.10	190.00	3.934
240.04	43.83	0.10	195.00	3.242
260.05	49.92	0.10	200.00	3.185
270.05	52.20	0.10	205.00	2.751
290.06	57.13	0.10	210.00	2.474
300.00	59.12	0.10	220.00	2.061
320.00	64.42	0.10	230.00	1.548
360.00	69.97	0.10	240.00	0.945
462.50	71.43	0.10	250.00	0.617
502.50	74.26	0.10	260.00	2.736
522.50	72.73	0.10	270.00	2.100
540.00	72.69	0.10	290.00	2.428
560.00	72.65	0.00	300.00	2.217
590.00	76.20	0.10	320.00	2.006
600.00	70.55	0.10	350.00	1.977