

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	E-Z Lock SMA-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
1.0	0.00	52.6	55.8
5.0	0.01	50.4	52.4
9.0	0.01	49.2	50.6
10.0	0.01	48.9	50.3
50.0	0.02	43.4	42.9
90.0	0.04	40.9	39.9
100.0	0.04	40.6	39.5
300.0	0.07	43.6	43.8
500.0	0.08	37.5	36.2
700.0	0.10	33.1	33.4
900.0	0.11	38.6	39.2
1000.0	0.12	33.1	33.3
1500.0	0.16	26.8	27.0
2000.0	0.18	31.8	33.8
2500.0	0.21	28.5	28.9
3000.0	0.24	26.4	27.3
3500.0	0.25	41.6	47.7
4000.0	0.28	27.9	28.7
4500.0	0.30	33.6	32.6
5000.0	0.32	34.8	37.0
5500.0	0.34	27.8	27.2
6000.0	0.36	32.1	30.5
6500.0	0.36	28.8	29.3
7000.0	0.37	29.1	27.0
7500.0	0.41	29.7	31.7
8000.0	0.44	24.4	23.1
8500.0	0.44	30.4	33.0
9000.0	0.47	22.3	22.0
9500.0	0.47	26.1	26.8
10000.0	0.49	21.3	22.8
11000.0	0.53	22.4	24.8
12000.0	0.55	24.9	26.7
13000.0	0.59	20.9	21.4
14000.0	0.64	18.6	18.9
15000.0	0.65	19.9	21.0
16000.0	0.67	25.8	26.9
17000.0	0.71	27.2	26.1
18000.0	0.83	19.1	19.9