

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	110.61	0.00	110	15.36
10	95.77	0.00	115	13.71
35	73.76	0.03	120	12.53
55	49.48	0.10	125	11.49
60	44.09	0.14	130	10.71
70	33.26	0.26	135	10.09
85	15.89	1.06	140	9.69
100	2.35	20.32	145	9.33
110	1.64	15.87	150	9.07
158	1.07	26.89	153	8.96
205	1.56	19.43	158	8.78
225	5.22	4.25	160	8.73
250	16.72	0.85	163	8.69
290	31.19	0.34	168	8.59
325	40.33	0.23	170	8.59
375	49.85	0.18	175	8.59
450	59.97	0.15	180	8.67
500	64.72	0.16	185	8.79
800	82.84	0.30	190	9.00
1000	74.70	0.40	195	9.31
1200	73.00	0.52	198	9.57
1300	72.97	0.54	200	9.81
1400	72.38	0.57	202	10.06
1500	74.09	0.59	205	10.55