

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	101.15	0.04	340	7.57
20	79.28	0.06	344	7.38
50	66.89	0.12	346	7.25
90	55.98	0.17	350	7.10
120	50.66	0.21	352	7.05
160	44.67	0.26	354	7.00
220	39.78	0.41	356	6.96
260	34.65	0.72	358	6.89
280	17.53	1.29	360	6.91
300	5.02	5.70	362	6.89
330	1.63	26.17	364	6.88
360	1.68	14.57	366	6.89
370	1.77	13.71	368	6.90
380	1.88	13.56	370	6.94
410	4.29	6.31	372	7.06
440	15.86	1.37	374	7.06
490	35.82	0.56	376	7.15
510	44.18	0.46	378	7.24
540	65.84	0.38	380	7.35
700	68.17	0.24	382	7.47
800	63.07	0.20	384	7.63
1000	56.52	0.17	386	7.76
1300	57.03	0.13	388	8.00
1600	69.65	0.15	390	8.21