

Fixed Attenuator

RCAT-09+

Typical Performance Data

FREQUENCY (GHz)	ATTENUATION (dB)	RETURN LOSS (dB)
0.05	9.01	31.32
0.5	9.02	33.70
1.0	9.03	32.89
1.5	9.05	31.20
2.0	9.07	29.41
2.5	9.08	27.79
3.0	9.10	26.46
3.5	9.13	25.38
4.0	9.16	24.42
4.5	9.20	23.58
5.0	9.23	22.90
5.5	9.27	22.32
6.0	9.30	21.84
6.5	9.34	21.44
7.0	9.38	21.05
7.5	9.43	20.72
8.0	9.47	20.45
8.5	9.52	20.24
9.0	9.57	20.23
9.5	9.61	20.10
10.0	9.67	20.03
10.5	9.71	19.82
11.0	9.77	19.66
11.5	9.84	19.61
12.0	9.89	19.49
12.5	9.94	19.44
13.0	9.98	19.32
13.5	10.04	19.12
14.0	10.12	18.90
14.5	10.18	18.74
15.0	10.27	18.39
15.5	10.34	18.12
16.0	10.47	17.80
16.5	10.56	17.66
17.0	10.63	17.55
17.5	10.67	17.33
18.0	10.67	17.03
18.5	10.77	16.67
19.0	10.87	16.43
19.5	10.95	16.37
20.0	11.06	16.29

