

Fixed Attenuator

RCAT-15+

Typical Performance Data

FREQUENCY (GHz)	ATTENUATION (dB)	RETURN LOSS (dB)
0.05	15.03	29.39
0.50	15.04	31.57
1.00	15.05	31.76
1.50	15.07	31.28
2.00	15.09	30.38
2.50	15.11	29.32
3.00	15.14	28.30
3.50	15.18	27.39
4.00	15.22	26.50
4.50	15.27	25.64
5.00	15.31	24.89
5.50	15.37	24.22
6.00	15.42	23.61
6.50	15.48	23.06
7.00	15.54	22.46
7.50	15.61	21.92
8.00	15.69	21.42
8.50	15.77	20.98
9.00	15.85	20.71
9.50	15.92	20.29
10.00	16.04	19.95
10.50	16.11	19.46
11.0	16.22	19.05
11.5	16.34	18.75
12.0	16.43	18.42
12.5	16.54	18.14
13.0	16.63	17.84
13.5	16.74	17.52
14.0	16.91	17.19
14.5	17.01	16.95
15.0	17.23	16.56
15.5	17.38	16.28
16.0	17.66	16.01
16.5	17.85	15.88
17.0	18.01	15.75
17.5	18.11	15.55
18.0	18.12	15.32
18.5	18.41	14.98
19.0	18.61	14.78
19.5	18.79	14.70
20.0	19.02	14.61

