

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.5	123.98	0.03	300	3.17
100	76.86	0.05	360	15.67
200	65.32	0.18	400	4.18
300	69.58	0.45	410	4.85
360	71.16	0.64	426	7.04
400	31.80	0.87	438	9.76
410	25.28	1.00	440	10.22
426	15.60	1.55	450	11.02
438	8.97	3.25	456	10.01
440	7.99	3.80	460	9.11
450	4.14	8.66	470	7.08
456	2.79	13.86	500	4.40
460	2.24	18.68	550	2.87
470	1.54	23.88	600	2.10
500	0.98	20.20	700	1.37
550	0.65	34.47	800	1.01
600	0.52	24.60	900	0.83
700	0.41	31.40	1000	0.72
800	0.36	28.31	1200	0.56
900	0.33	23.11	1300	0.51
1000	0.31	21.77	1400	0.5
1300	0.32	25.18	1500	0.45
1800	0.36	19.19	1800	0.41
2000	0.53	15.69	2000	0.32