

High Pass Filter

SCHF-EDU0288

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.10	74.42	0.00	5.00	210.27
0.50	59.96	0.00	5.50	11.15
1.00	54.57	0.00	6.00	115.47
2.00	52.08	0.01	6.20	147.76
4.00	78.81	0.05	6.40	185.22
5.00	70.20	0.14	6.60	246.05
5.10	68.26	0.15	6.90	376.07
5.20	64.45	0.15	7.00	416.66
5.50	52.00	0.20	7.20	447.04
5.60	47.99	0.22	7.40	386.84
5.70	44.22	0.24	7.60	309.11
5.80	40.70	0.27	7.80	251.33
5.90	37.32	0.29	8.00	212.42
6.00	34.10	0.34	8.10	195.69
6.10	30.98	0.38	8.20	183.50
6.20	27.95	0.44	8.30	170.65
6.40	22.08	0.63	8.40	163.77
6.60	16.47	0.96	8.50	153.23
7.00	6.50	3.65	8.60	145.49
7.20	3.34	7.99	8.70	137.12
7.40	1.84	16.48	8.80	131.09
8.00	0.89	21.93	8.90	123.09
8.50	0.63	33.89	9.00	117.97
10.00	0.43	17.68	10.00	79.08
100.00	0.12	24.31	50.00	2.90
200.00	0.15	26.72	100.00	0.97
500.00	0.26	23.39	500.00	0.49
1000.00	0.81	17.83	1000.00	0.53
2000.00	1.15	13.43	2000.00	0.58
3000.00	4.00	17.56	3000.00	0.96