

RF Transformer

SCTX4-32HP-20W+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1	0.17	20.57
5	0.20	30.42
9	0.17	32.79
13	0.16	34.25
17	0.16	34.94
21	0.15	35.09
25	0.15	35.08
29	0.16	35.18
30	0.16	35.18
33	0.16	35.02
36	0.16	34.93
39	0.16	34.75
42	0.16	34.65
45	0.16	34.50
48	0.16	34.40
51	0.17	34.31
54	0.17	34.17
57	0.17	33.98
60	0.17	33.90
63	0.18	33.66
66	0.18	33.47
69	0.18	33.21
72	0.18	33.09
75	0.19	32.88
78	0.19	32.69
81	0.19	32.60
84	0.20	32.36
87	0.20	32.14
88	0.20	32.04
90	0.21	31.93
100	0.22	31.23
130	0.25	28.86
160	0.29	27.77
190	0.33	25.54
220	0.38	23.53
250	0.43	21.43
280	0.50	19.39
310	0.58	17.40
340	0.69	15.49
370	0.83	13.61
400	1.03	11.81