

Adapter, SMA-Female Flange to SMA-Male**SFFL-SM50+****Typical Performance Data**

FREQ.	INSERTION LOSS	SMA-FEMALE VSWR	SMA-MALE VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	0.00	1.00	1.00
0.05	0.00	1.00	1.00
0.07	0.01	1.00	1.00
0.10	0.01	1.00	1.00
0.20	0.01	1.01	1.01
0.30	0.02	1.01	1.01
0.40	0.03	1.01	1.01
0.50	0.03	1.01	1.01
0.60	0.03	1.01	1.01
0.70	0.03	1.01	1.01
0.80	0.03	1.01	1.01
0.90	0.04	1.01	1.01
1.00	0.04	1.01	1.01
2.00	0.05	1.01	1.01
3.00	0.06	1.01	1.02
4.00	0.06	1.02	1.03
5.00	0.06	1.02	1.03
6.00	0.06	1.01	1.01
7.00	0.06	1.02	1.02
8.00	0.06	1.03	1.03
9.00	0.06	1.03	1.03
10.00	0.06	1.04	1.04
11.00	0.06	1.06	1.06
12.00	0.06	1.04	1.04
13.00	0.06	1.04	1.04
14.00	0.06	1.09	1.09
15.00	0.07	1.12	1.12
16.00	0.07	1.10	1.10
17.00	0.06	1.05	1.04
18.00	0.07	1.08	1.08