

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.22	31.25	30.48
0.1	0.70	45.00	39.48
0.2	0.99	37.21	42.33
0.4	1.41	47.17	45.63
0.6	1.73	42.88	42.72
0.8	2.00	39.78	39.15
1.0	2.24	49.70	53.85
1.5	2.75	35.31	34.61
2.0	3.18	52.52	38.29
2.5	3.57	31.46	31.26
3.0	3.91	32.56	31.91
3.5	4.23	30.13	29.74
4.0	4.53	26.73	26.75
4.5	4.81	30.88	30.16
5.0	5.09	25.13	25.01
5.5	5.35	26.83	25.79
6.0	5.59	28.68	26.30
6.5	5.84	24.26	23.26
7.0	6.06	27.78	25.66
7.5	6.28	27.74	25.51
8.0	6.50	25.53	23.29
8.5	6.70	29.33	25.74
9.0	6.91	31.52	23.64
9.5	7.11	28.64	23.18
10.0	7.31	36.66	24.18
10.5	7.50	38.89	24.68
11.0	7.70	31.15	23.32
11.5	7.89	30.93	23.10
12.0	8.06	38.20	24.40
12.5	8.26	28.30	22.93
13.0	8.45	26.35	23.20
13.5	8.61	29.86	27.38
14.0	8.81	25.35	23.38
14.5	8.99	24.32	22.44
15.0	9.14	28.80	25.10
15.5	9.33	24.46	22.81
16.0	9.52	23.17	22.34
16.5	9.66	25.87	25.86
17.0	9.85	22.69	22.14
17.5	10.00	22.16	24.67
18.0	10.12	25.55	29.15

