

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.30	90.67	0.03	7	178.47
0.60	98.58	0.02	8	103.59
0.90	105.30	0.02	9	70.18
1.00	94.54	0.02	10	54.87
1.20	84.29	0.01	11	43.04
2.00	63.48	0.03	12	34.88
3.00	46.54	0.07	13	28.98
3.22	43.89	0.08	14	24.54
4.76	45.58	0.26	15	21.07
4.98	30.74	0.32	16	18.32
5.26	20.70	0.47	17	16.09
6.00	4.13	3.72	18	14.24
6.08	3.18	4.83	19	12.74
6.20	2.13	6.92	20	10.55
7.00	0.46	32.95	21	10.06
10.00	0.20	25.59	22	9.57
30.00	0.07	38.05	23	9.03
50.00	0.08	35.15	24	8.46
100.00	0.10	32.42	25	7.91
200.00	0.15	27.82	26	7.29
350.00	0.22	23.19	27	6.72
400.00	0.24	22.07	28	6.22
500.00	0.30	20.09	29	5.78
600.00	0.37	18.45	30	5.38