

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.05	1.34	8.81
0.06	1.05	10.06
0.07	0.86	11.16
0.08	0.70	12.14
0.09	0.60	13.01
0.10	0.53	13.84
0.20	0.31	18.41
0.30	0.26	20.16
0.40	0.26	20.91
0.50	0.26	21.31
1.00	0.24	22.05
10.00	0.17	23.59
29.00	0.18	23.40
48.00	0.20	22.74
67.00	0.22	21.88
86.00	0.23	20.93
105.00	0.24	19.94
124.00	0.24	18.97
143.00	0.25	18.03
162.00	0.26	17.11
181.00	0.27	16.21
200.00	0.28	15.35
225.00	0.30	14.27
250.00	0.32	13.26
275.00	0.33	12.31
300.00	0.35	11.39
320.00	0.37	10.69
340.00	0.40	10.01
360.00	0.45	9.37
380.00	0.48	8.76
400.00	0.52	8.20
420.00	0.58	7.67
440.00	0.67	7.14
460.00	0.76	6.64
480.00	0.83	6.17
500.00	0.94	5.73
520.00	1.11	5.34
540.00	1.28	4.96
560.00	1.43	4.66
580.00	1.61	4.36
600.00	1.83	4.07