

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.07	2.74	5.10
0.08	2.38	5.85
0.09	2.09	6.56
0.10	1.86	7.24
0.20	0.94	12.00
0.30	0.75	14.43
0.40	0.69	15.77
0.50	0.66	16.54
1.00	0.58	18.12
5.00	0.39	20.92
10.00	0.39	21.11
14.00	0.40	20.85
18.00	0.42	20.44
22.00	0.44	19.94
26.00	0.45	19.39
30.00	0.47	18.83
34.00	0.49	18.25
38.00	0.51	17.69
42.00	0.53	17.16
46.00	0.55	16.65
50.00	0.57	16.15
55.00	0.60	15.55
60.00	0.63	14.99
65.00	0.66	14.46
70.00	0.69	13.96
75.00	0.72	13.48
80.00	0.75	13.04
85.00	0.78	12.62
90.00	0.81	12.21
95.00	0.84	11.83
100.00	0.88	11.46
110.00	0.95	10.79
120.00	1.02	10.17
130.00	1.08	9.60
140.00	1.14	9.09
150.00	1.20	8.61
160.00	1.26	8.17
170.00	1.32	7.77
180.00	1.38	7.39
190.00	1.44	7.04
200.00	1.49	6.72