

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.05	2.19	7.55
0.06	1.81	8.87
0.08	1.56	9.99
0.09	1.39	10.94
0.10	1.28	11.77
0.20	0.92	15.36
0.30	0.80	16.90
0.40	0.73	17.86
0.50	0.67	18.59
0.63	0.62	19.30
0.75	0.58	19.88
0.88	0.55	20.36
1.00	0.53	20.76
4.00	0.41	23.35
7.00	0.40	23.59
10.00	0.41	23.47
30.00	0.46	20.82
50.00	0.50	18.03
70.00	0.54	15.79
76.00	0.56	15.21
82.00	0.58	14.66
88.00	0.60	14.15
94.00	0.61	13.66
100.00	0.63	13.21
108.00	0.66	12.63
116.00	0.69	12.11
124.00	0.71	11.61
132.00	0.74	11.13
140.00	0.76	10.69
148.00	0.79	10.29
156.00	0.81	9.90
164.00	0.83	9.53
172.00	0.85	9.22
180.00	0.87	8.88
190.00	0.89	8.49
200.00	0.92	8.12
210.00	0.95	7.76
220.00	0.98	7.44
230.00	1.00	7.13
240.00	1.01	6.84
250.00	1.02	6.56