

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.20	1.37	11.78
0.30	1.18	13.75
0.40	1.07	14.96
0.50	1.01	15.82
0.63	0.93	16.67
0.75	0.88	17.39
0.88	0.84	17.98
1.00	0.80	18.51
2.00	0.66	21.14
10.00	0.53	24.51
90.00	0.57	20.65
122.00	0.60	18.31
154.00	0.62	16.06
186.00	0.63	13.98
218.00	0.65	12.09
250.00	0.68	10.45
270.00	0.70	9.53
290.00	0.72	8.60
310.00	0.73	7.80
330.00	0.77	7.07
350.00	0.82	6.41
365.00	0.83	5.95
380.00	0.86	5.52
395.00	0.89	5.13
410.00	0.90	4.76
425.00	0.95	4.42
440.00	1.01	4.12
455.00	1.04	3.83
470.00	1.08	3.58
485.00	1.10	3.37
500.00	1.17	3.18
510.00	1.20	3.06
520.00	1.27	2.95
530.00	1.31	2.83
540.00	1.36	2.71
550.00	1.41	2.61
560.00	1.44	2.49
570.00	1.50	2.41
580.00	1.54	2.32
590.00	1.60	2.24
600.00	1.66	2.16